Color Availability: White • Black

Installation Instructions

13/16'

dia. hole

for Tresco® International's

Rocker Switch Kit

Recess

Switch

Wiring Block

#5


Mounted Rocker


Tresco® International offers rocker and automatic switches to control 12V lighting. Switches can be placed between wiring block and ELT60-CON transformer (sold separately) to control all the lights on one system, or between light and wiring block for isolated control of each light.

Option 1

To control all lights from (1) switch and (1) ELT60-CON transformer: Before beginning any wiring, be sure power is turned OFF to transformer:

- 1. Determine location of switch and transformer. (see installation instructions for ELT60-CON transformer on reverse side)
- 2. Check wire length from the switch to the transformer. If too short, order a 12V extension cord from Tresco International. (Max. length for total cord is 5 meters.)
- 3. To recess mount the switch: Drill 13/16" hole for switch. Place wires through hole and plug into switch. Push switch completely into hole until snug.
- 4. Disconnect wiring block from transformer and plug wiring block into female end of switch. Plug male end of switch into female end of transformer (12V side).
- 5. Connect lights into wiring block. Transformer supplies power to 60W maximum: (3) 20W lights or (6) 10W lights. Minimum load 20W.
- 6. Turn power on to transformer.





(#3

- 3. Plug male end of switch into wiring block. Plug light into female end of switch.
- 4. Follow steps above for additional lights and switches.
- 5. Turn power on to transformer.

Accessories available from Tresco International:

- Touch Dimmer Uses a conveniently located touch pad to turn lighting Lo/Med/Hi/Off. Can control up to three transformers and their lights.
- 12V Extension Cords 1, 2 and 3 meter cords. Maximum recommended length from light to transformer is 5 meters.

See ELT60-CON transformer installation instructions on reverse side.

Save these instructions for future reference. For technical assistance: 1-800-227-1171







Tresco International Ltd. Co.

P.O. Box 5100

Poland, Ohio USA 44514

Tel: Fax: 800-227-1171 800-841-2523

Tel: Fax: 330-549-2230 330-549-2260

E-mail:

tresco@cboss.com

Web:

www.trescointernational.com

© 2002, Tresco International Printed in USA 103/GRX-HF